

RF Cable Assembly

TL-8A-11N-11N-00600-51 Item: 84236770

Description

Test assembly for indoor applications (Test and Measurement) consisting of a high flexible PE foamed cable with armouring protection and 2x N male straight connectors for frequency up to 8.0 GHz.



Product Configuration

Cable	TL-8A		
Type Description Connector A	11_N-50-4-21		
Series Connector A	N	plug	straight
Type Description Connector B	11_N-50-4-21		
Series Connector B	N	plug	straight
Armour	Steel wire spring, steel braid, TPU jacket blue		
Length	600 mm REF to REF		

Technical Data

Electrical Data		
Impedance	50 Ω	
Operating Frequency (max.)	8 GHz	
Return Loss (min.)	-22 dB	VSWR : 1.173
Insertion Loss (max)	0.88 dB	
Signal delay	4.12 ns/m	
Velocity of propagation	81 %	
CW power (at 40°C)	50 W at 8 GHz	
Amplitude stability vs. Flexure	±0.2 dB	
Phase stability vs. Flexure	2.5 ° / GHz	
Mechanical Data		
Diameter cable	10.3 mm	
Bending radius static (min.)	55 mm	
Weight	0.17 kg	
Environmental Data		
Operating temperature	-40 °C to + 85 °C	
2011/65/EU (RoHS)	compliant	
2012/19/EU (WEEE)	relevant	
2006/1907/EC (REACH)	compliant	