

## Coaxial Cable Connector 11\_BNC-50-4-4/133\_N

### Description

Straight cable plug

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

|                          |       |
|--------------------------|-------|
| Impedance                | 50 Ω  |
| Interface frequency max. | 4 GHz |

#### Mechanical Data

|                |           |
|----------------|-----------|
| Centre contact | crimped   |
| Outer contact  | crimped   |
| Weight         | 0.0108 kg |

#### Environmental Data

|                                                      |                  |
|------------------------------------------------------|------------------|
| Operating temperature                                | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

| Piece Parts    | Material              | Surface Plating                   |
|----------------|-----------------------|-----------------------------------|
| Centre contact | Brass                 | Gold Plating (Nickel underplated) |
| Outer contact  | Brass                 | SUCOPLATE (R) Plating             |
| Body           | Brass                 | SUCOPLATE (R) Plating             |
| Insulator      | PFA / PTFE            |                                   |
| Coupling nut   | Brass                 | SUCOPLATE (R) Plating             |
| Gasket         | VMQ (Silicone rubber) |                                   |
| Crimp ferrule  | Copper                | SUCOPLATE (R) Plating             |

### Related Documents

|                      |                |
|----------------------|----------------|
| Outline drawing      | DOU-00071226   |
| Catalogue drawing    | DCA-00006189   |
| Assembly instruction | DOC-0000179061 |

### Ordering Information

|                      |                      |
|----------------------|----------------------|
| Single package       | 11_BNC-50-4-4/133_NE |
| Bulk 100 pcs package | 11_BNC-50-4-4/133_NH |

### Additional Information

|                 |                     |
|-----------------|---------------------|
| Suitable cables | RG_59_B/U, GX_04273 |
|-----------------|---------------------|