

Coaxial Cable Connector 11_UHF-0-7-4/002_-

Description

Straight cable plug

Interface standards
IEC 60169-12



Technical Data

Electrical Data

Impedance	other Ω
Interface frequency max.	0.2 GHz

Mechanical Data

Centre contact	soldered
Outer contact	others
Weight	0.0232 kg

Environmental Data

Operating temperature	-55 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PSU (Polysulfone)	
Coupling nut	Brass	Nickel Plating

Related Documents

Catalogue drawing	DOU-00007551
Assembly instruction	DOC-0000201026

Ordering Information

Single package	11_UHF-0-7-4/002_-E
----------------	---------------------

Additional Information

Suitable cables	RG_213_/U, GX_07272
-----------------	---------------------