

Coaxial Cable Connector 16_MM CX-50-1-12/111_O

Description

Right angle cable plug

Interface standards

SUHNER-MM CX

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0003 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00007190
Catalogue drawing	DCA-00094523
Assembly instruction	DOC-0000180777

Ordering Information

Bulk 100 pcs package	16_MM CX-50-1-12/111_OH
Single package	16_MM CX-50-1-12/111_OE

Additional Information

Suitable cables	EZ_47_TP_M17, SU CO FORM_47_CU
-----------------	--------------------------------