

Coaxial Cable Connector 11_BNC-50-3-54/103_N

Description

Straight cable plug

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0096 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00006656
Catalogue drawing	DOU-00006658
Assembly instruction	DOC-0000180227

Ordering Information

Single package	11_BNC-50-3-54/103_NE
----------------	-----------------------

Additional Information

Suitable cables	EZ_141_TP_M17, SUCOFORM_141
-----------------	-----------------------------