

Coaxial Cable Connector
24_N-50-7-34/133_N

Description

Straight bulkhead cable feed through

Interface standards
IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω			
Interface frequency max.	11 GHz			
Frequency range	DC to 2 GHz	2 to 4 GHz		4 to 6 GHz
Return loss	31.8 dB	31 dB		24 dB

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0388 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00240912
Assembly instruction	DOC-0000418501
Mounting hole	DOU-00240912

Ordering Information

Tray package	24_N-50-7-34/133_NY
--------------	---------------------

Additional Information

Suitable cables	SPUMA_400, SPUMA_400-FR-01, Spuma_400-RS-FR, LMR-400
-----------------	--