


Coaxial Panel Connector
13_716-50-0-4/003_-

Description

Straight panel receptacle plug, flange mount

Interface standards
IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 7.5 GHz

Mechanical Data

Number of matings 500
Weight 0.0981 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing DOU-00011259
Catalogue drawing DCA-00011261

Ordering Information

Bulk 20 pcs package 13_716-50-0-4/003_-V