

Coaxial Cable Connector 16_SMA-50-3-100/199_N

Description

Right angle cable plug

Interface standards
SUHNER-SMA-26.5GHz

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	26.5 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0056 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Other body part	Brass	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	

Related Documents

Catalogue drawing	DCA-00008255
Assembly instruction	DOC-0000179435

Ordering Information

Single package	16_SMA-50-3-100/199_NE
----------------	------------------------

Additional Information

Suitable cables	EZ_141_TP_M17, SUCOFORM_141, MULTIFLEX_141
-----------------	--