

Between Series Adaptor 33_QMA-SMA-50-1/133_N

Description

Adaptor plug/jack
QMA plug (male) / SMA jack (female)

QuickLock Interface

Interface standards

Series QMA - QMA QLF compliant

Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	18 GHz	
Frequency range	DC to 4 GHz	4 to 6 GHz
Return loss	≥ 32 dB	≥ 22 dB

Mechanical Data

Number of matings	100
Weight	0.0067 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - QMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00014655
-----------------	--------------

Ordering Information

Single package	33_QMA-SMA-50-1/133_NE
----------------	------------------------