

## Coaxial Panel Connector 22\_SHV-50-0-2/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

IEC 60498\_MIL-STD-348A/314



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	0.3 GHz

#### Mechanical Data

Chassis torque	2 Nm
Number of matings	500
Weight	0.0115 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00010447
Catalogue drawing	DCA-00010449
Mounting hole	DOU-00008762

### Ordering Information

Single package	22_SHV-50-0-2/133_NE
----------------	----------------------

### Remarks

High voltage connector Working voltage (at sea level) 3.5 kV rms