

Within Series Adaptor 45_QLA-01-0-1/112_N

Description

T-adaptor, 1 plug, 2 jacks, asymmetric
QLA-01 plug (male) / QLA-01 jack (female)

Interface standard
Series QLA-01 - NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance	other Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Number of matings	10000
Weight	0.0076 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	not compliant

Material Data

Interface - QLA-01 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	Nickel Plating

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00013488
-------------------	--------------

Ordering Information

Single package	45_QLA-01-0-1/112_NE
----------------	----------------------