

Coaxial Cable Connector 11_MCX-50-2-15/133_N

Description

Straight cable plug

Interface standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0008 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00006602
Catalogue drawing	DOU-00006606
Assembly instruction	DOC-0000180174

Ordering Information

Bulk 100 pcs package	11_MCX-50-2-15/133_NH
----------------------	-----------------------

Additional Information

Suitable cables	ENVIROFLEX_316_D, K_02252_D, G_02232_D
-----------------	--