

Coaxial Cable Connector 11_BNC-50-7-1/133_N

Description

Straight cable plug

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0367 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00008406
Catalogue drawing	DOU-00006636
Assembly instruction	DOC-0000179854

Ordering Information

Single package	11_BNC-50-7-1/133_NE
----------------	----------------------

Additional Information

Suitable cables	RG_213_/U, GX_07272, G_07262
-----------------	------------------------------