

Coaxial Cable Connector
24_TNC-50-7-5/133_N

Description

Straight bulkhead cable feed through

Interface standards
IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	29 dB	28 dB	23 dB

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.02816 kg

Environmental Data

Operating temperature	65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00240997
Assembly instruction	DOC-0000452674
Mounting hole	DOU-00008751

Ordering Information

Single package	24_TNC-50-7-5/133_NE
----------------	----------------------

Additional Information

Suitable cables	SPUMA_400, SPUMA_400-FR-01, Spuma_400-RS-FR
-----------------	---