

## Coaxial Cable Connector 11\_UHF-0-7-17/033\_-

### Description

Straight cable plug

Interface standards  
IEC 60169-12



### Technical Data

#### Electrical Data

|                          |                |
|--------------------------|----------------|
| Impedance                | other $\Omega$ |
| Interface frequency max. | 0.2 GHz        |

#### Mechanical Data

|                |           |
|----------------|-----------|
| Centre contact | crimped   |
| Outer contact  | crimped   |
| Weight         | 0.0238 kg |

#### Environmental Data

|                                                         |                  |
|---------------------------------------------------------|------------------|
| Operating temperature                                   | -55 °C to 165 °C |
| 2011/65/EU (RoHS - including<br>2015/863 and 2017/2102) | compliant        |

#### Material Data

| Piece Parts    | Material          | Surface Plating       |
|----------------|-------------------|-----------------------|
| Centre contact | Brass             | Silver Plating        |
| Outer contact  | Brass             | SUCOPLATE (R) Plating |
| Body           | Brass             | SUCOPLATE (R) Plating |
| Insulator      | PSU (Polysulfone) |                       |
| Coupling nut   | Brass             | SUCOPLATE (R) Plating |
| Crimp ferrule  | Copper            | SUCOPLATE (R) Plating |

### Related Documents

|                      |                |
|----------------------|----------------|
| Outline drawing      | DOU-00181576   |
| Catalogue drawing    | DCA-00045040   |
| Assembly instruction | DOC-0000201061 |

### Ordering Information

|                |                      |
|----------------|----------------------|
| Single package | 11_UHF-0-7-17/033_-E |
|----------------|----------------------|

### Additional Information

|                 |                                                     |
|-----------------|-----------------------------------------------------|
| Suitable cables | RG_213_/U, GX_07272, G_07262, G_07272, RADOX_RF_213 |
|-----------------|-----------------------------------------------------|