



Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Locking system	Push-pull

Technical details

Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	0A.250 - 1 Coax (50 Ohm)
Contact Type	Solder

Form & Material

Shell style / Model id	ABF - Adapter
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	10.45 g

https://www.lemo.com/int_en/abf-0a-250-cta.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Environmental protection	IP50
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	----------------------------------------------

Drawings

