



- NOTES:
- 1. ALL PARTS TO BE BULK PACKED.
 - 2. SEE DRAWING HPMISTD FOR HOLE PATTERN.
 - 3. ALL DIMENSIONS ARE REFERENCE ONLY. DIMENSIONS IN [] ARE METRIC.



SHOWN ASSEMBLED KIT
ASSY: W6380-2PG-P-3XX SHOWN




DAISY CHAIN GROMMETS (**3DC**)
.125 I.D. FOR CABLES .09-.14 [2.3 - 3.6] O.D.
.188 I.D. FOR CABLES .18-.20 [4.6 - 5.1] O.D.
.250 I.D. FOR CABLES .24-.26 [6.1 - 6.6] O.D.


CABLE-END CONNECTOR P/N	CONTACTS
W6380-2PG-P-3XX	2 #16
W6380-3PG-P-3XX	3 #16
W6380-4PG-P-3XX	4 #16
W6380-XPG-P-3XX	

GROMMET SIZE:
3DC FOR DAISY CHAIN GROMMETS
3XX FOR SINGLE GROMMET SIZE PER LIST ON THIS DRAWING.

NUMBER OF CONTACTS



MATING FACE
ASSY: W6380-2PG-P-3XX SHOWN




CABLE-END ASSEMBLY KIT
MAT'L: BLACK THERMOPLASTIC HOUSING
BLACK THERMOPLASTIC COUPLING RING
RED SILICONE O-RING
STAINLESS STEEL SPRING

(2-4) #16 PIN CONTACT, CRIMP
MAT'L: COPPER ALLOY, GOLD PLATED


.430 [10.9]

.688 [17.5]




BACKSHELL
MAT'L: THERMOPLASTIC, BLACK

GROMMET
MAT'L: THERMOPLASTIC ELASTOMER, BLACK
GROMMET SINGLE SIZE = CABLE O.D. RANGE:
311: .125 I.D. FOR CABLES .09-.14 [2.3 - 3.6] O.D.
315: .156 I.D. FOR CABLES .15-.17 [3.8 - 4.3] O.D.
318: .188 I.D. FOR CABLES .18-.20 [4.6 - 5.1] O.D.
321: .225 I.D. FOR CABLES .21-.23 [5.3 - 5.8] O.D.



SHOWN ASSEMBLED KIT
ASSY: W6380-2PG-P-3XX SHOWN




WIRING END
ASSY: W6380-2PG-P-3XX SHOWN WITHOUT HARDWARE

CUSTOMER APPROVAL


THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____


DATE: _____



WIRING END
W6380-2PG-P-3XX



WIRING END
W6380-3PG-P-3XX



WIRING END
W6380-4PG-P-3XX

RoHS COMPLIANT

0A	PNK	05-10-19	PDR 16014
REV.	INIT.	DATE	DESCRIPTION
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.		ORIG. DRAWN BY: PNK DATE: 05-10-19	 601 E. WILDWOOD VILLA PARK, IL 60181
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.010 ANGLES ±1° FRACTIONS ±1/16		CHECKED BY:	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.		APPROVED BY:	TITLE: CABLE-END ASSEMBLY 2-4 #16 PIN CONTACTS, CRIMP INSTA-CLICK™ MINI-CON-X
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.010 ANGLES ±1° FRACTIONS ±1/16		SCALE: NTS SIZE: B SHEET: 1 OF 1	CUSTOMER: STANDARD PRODUCT
FILE: W6380-XPG-P-3XX		DIRECTORY: SLW	PART NUMBER: W6380-XPG-P-3XX
CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			REV 0A