





NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. SEE DRAWING HPMISTD FOR HOLE PATTERN.
3. ALL DIMENSIONS ARE REFERENCE ONLY.
DIMENSIONS IN [] ARE METRIC.



SHOWN ASSEMBLED KIT
ASSY: W6380-2SG-P-5XX SHOWN




MATING FACE
ASSY: W6380-2SG-P-5XX SHOWN



SHOWN ASSEMBLED KIT
ASSY: W6380-2SG-P-5XX SHOWN

CABLE-END CONNECTOR P/N	CONTACTS
W6380-2SG-P-5XX	2 #16
W6380-3SG-P-5XX	3 #16
W6380-4SG-P-5XX	4 #16
W6380-5SG-P-5XX	5 #16
W6380-XSG-P-5XX	

GROMMET SIZE
NUMBER OF CONTACTS




WIRING END
ASSY: W6380-2SG-P-5XX SHOWN WITHOUT HARDWARE


CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.


APPROVED BY: _____
DATE: _____




WIRING END
W6380-2SG-P-5XX



WIRING END
W6380-3SG-P-5XX



WIRING END
W6380-4SG-P-5XX



WIRING END
W6380-5SG-P-5XX

RoHS COMPLIANT

0A	PNK	01-15-18	PDR 16014
REV.	INIT.	DATE	DESCRIPTION
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: PNK DATE: 01-15-18 CHECKED BY:
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.010 ANGLES ±1° FRACTIONS ±1/16 CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			APPROVED BY:
FILE: W6380-XSG-P-5XX	DIRECTORY: SLW	SCALE: NTS SIZE: B SHEET: 1 OF 1	TITLE: CABLE-END ASSEMBLY 2-5 #16 SOCKET CONTACTS, CRIMP INSTA-CLICK™ MINI-CON-X CUSTOMER: STANDARD PRODUCT PART NUMBER: W6380-XSG-P-5XX
			REV 0A