

OS2 Duplex Single Mode 9 /125, OFNR, LC / LC, Fiber Optic Cable, FBR-512-XXM



LC TO LC DUPLEX SINGLE-MODE FIBER OPTIC CABLE

- Our high-quality 9/125 single-mode fiber cable with LC/LC connectors is perfect for fast Ethernet, gigabit Ethernet, and other data applications.
- Single-mode fiber cable is an ideal solution for long-range networking.
- OFNR (riser) rated fiber cable is ideal for use in upright shafts that run between floors in the building.
- The small LC connector is perfect for high-density network applications.
- Corning® glass 9µm core and 125µm cladding.
- Test report included in each cable package.
- UL listed

Fiber Connector :	LC to LC
Fiber Mode:	Single Mode, 9 / 125 µm
Fiber Count:	2 Strands
Polish Type:	UPC to UPC
Insertion Loss:	≤ 0.3 dB
Return Loss:	≥ 55 dB
Jacket OD:	2.0 mm
Jacket Material:	OFNR (Riser)
Jacket Color:	Yellow

without us, you are just not connected! ■