





DWG. NO.							
30 JR120							
DASH	MARKING	(A)	(B)	LONGEST CONTACT	LUG LOCATION	COMPONENTS	MATERIAL
-1	09922 30JR120-1	.831	1.297	CENTER	L1	BODY/FERRULES:	BRASS PER ASTM B 16
-2	09922 30JR120-2	.706	1.219	TAB	L1	INSULATORS:	PTFE FLUOROCARBON PER ASTM-D1710
-3	09922 30JR120-3	.706	1.219	TAB	L2	CENTER CONTACT:	BERYLLIUM COPPER PER ASTM B 196
-4	09922 30JR120-4	.706	1.219	TAB	L5		
-5	09922 30JR120-5	.831	1.297	CENTER	L2		
-6	09922 30JR120-6	.706	1.219	TAB	L1		
-7	09922 30JR120-7	.706	1.219	TAB	L5		
-8	09922 30JR120-8	.706	1.219	TAB	L4		
-9	09922 30JR120-9	.706	1.219	TAB	L2		

RECOMMENDED
PANEL CUTOUT

"L4" LUG
LOCATION SHOWN



LINEAR MEASURE:	(INCH mm)	INCH [mm]
THIRD ANGLE PROJECTION		
		
TOLERANCES UNLESS OTHERWISE SPECIFIED		
No. OF PLACES	INCH [mm]	
ONE PLACE	±.1 [±.3]	
TWO PLACES	±.002 [±.5]	
THREE PLACES	±0.010 [±.25]	
ANGLES±1°		

DRAWING TITLE		BNC TRIAX JACK RECEPTACLE	
CAT NO.		30JR120-	
CAGE NO: 09922	SIZE: B		
CUSTOMER			
		INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994	
www.souriau.com			
30JR120 B		APPROVAL	
		DRAWN: DS	11-19-04
		CHKD: BM	11-19-04
		DSGN: RL	11-19-04
		MFG: RR	11-19-04
QC: DK	11-19-04		
DRAWING SCALE: N/A			
DRAWING NO.		REV	
1 OF 1			