



Unthreaded Spacer - Inside Diameter - 1.8 mm | 0.071 in; Outside Diameter - 4.5 mm | 0.177 in 0.177 in; Ceramic

Ceramic insulation bead to provide protection and insulation. Highly heat and voltage resistant, can be stacked together for longer wire assemblies.



Item code: CER-5

● Request the lead time [here](#)

For more information [Delivery & returns](#)

Quantity	Unit price
1000 - 9999	\$0.3461
10000 - 24999	\$0.2519
25000+	\$0.2311

Total price:

\$346.10

1000 x

\$0.3461

Quantity

1000

Standard pack: 1000
Order in multiple of 1000

Add to cart

Add item to list

Order sample:

1

Add sample +

Download CAD

Request a quote

Useful Information

Documents

[Material Data Sheet](#)

[Technical Drawing](#)

Specifications

Inside Diameter	0.071 in
Maximum Operating Temperature	3092 °F
Minimum Operating Temperature	-40 °F
Operating Temperature Range	-40 - 3092 °F
Outside Diameter	0.177 in
Spacer Length	0.177 in
Color	Natural
Full Material	C220 Steatite Ceramic
Spacer Shape	Round

Can't find what you're looking for? Tell us what you are looking for...

Send us your inquiry and we'll get back to you in 24 hours.

Contact us

Recently viewed items

Unthreaded Spacer - Inside Diameter
- 1.8 mm | 0.071 in...

[See our selection](#) →