





## NOTE:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.
2. MATERIAL: HIGH TEMPERATURE THERMOPLASTIC UL94 V-0.
3. BULKHEAD THICKNESS RANGE: 0.79 - 2.54
4. APPLICABLE COMPONENTS
  - a) APPLICABLE POWER CRIMP CONTACT: 10134849-\*
  - b) APPLICABLE CONTACT SECONDARY LOCK: 10073097-DGC004LF
  - c) APPLICABLE SIGNAL CONTACT: 76808-DGC\*\*\*LF
  - d) APPLICABLE SIGNAL CONTACT IMLA: 10097392-DGC001LF (USAGE OF IMLA: SIGNAL PIN=1:4)
5. PRODUCT SPEC: GS-12-1267
6. APPLICATION SPEC: GS-20-0426
7. CONTACT CRIMPING APPLICATION SPEC: GS-20-0435

spec ref	See Notes		dr	Rainbow Zhan	2016/03/02	projection	MM	size	A4	scale
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Rainbow Zhan	2016/04/22			ecn no	-	
See Notes			chr	Cheng-Ling Tao	2016/04/21			rel level	Released	
surface	✓	linear	appr	Pei-Ming Zheng	2016/04/22	product family		dwg no	10129413-018	rev
		0.X	±0.50	Amphenol FCi		8P+24S PMT				A
		0.XX	±0.25	+		PwrBlade+ Cable Plug Housing				
		0.XXX	±0.10							
		angular	0°	±2°	www.fci.com	cat. no.	Product - Customer Drw		sheet 2 of 2	