




PRODUCT NUMBER

10136956-001LF

WIRING DIAGRAM

P1 PIN NO.	P2 PIN NO.	WIRE SIZE	WIRE COLOR
12	1	16 AWG	BLACK
11	2	16 AWG	BLACK
10	3	16 AWG	BLACK
9	4	16 AWG	BLACK
8	5	16 AWG	BLACK
7	6	16 AWG	BLACK
6	7	16 AWG	BLACK
5	8	16 AWG	BLACK
4	9	16 AWG	BLACK
3	10	16 AWG	BLACK
2	11	16 AWG	BLACK
1	12	16 AWG	BLACK
24	13	16 AWG	BLACK
23	14	16 AWG	BLACK
22	15	16 AWG	BLACK
21	16	16 AWG	BLACK
20	17	16 AWG	BLACK
19	18	16 AWG	BLACK
18	19	16 AWG	BLACK
17	20	16 AWG	BLACK
16	21	16 AWG	BLACK
15	22	16 AWG	BLACK
14	23	16 AWG	BLACK
13	24	16 AWG	BLACK



NOTE:

1. RATED CURRENT PER PIN: 8A MAX.
2. P1 CAN MATE WITH FCI MINITEK PWR3.0 HIGH CURRENT CONNECTORS
BASE NO.: 10132449F (R/A) OR 10132450 (V/T)
3. P2 CAN MATE WITH FCI MINITEK PWR4.2 HIGH CURRENT CONNECTORS
BASE NO.: 10131318 (R/A) OR 10131319 (V/T)

(P) IBM PN: 01EJ331
IBM FRU PN: 01EJ362
EC: M14878

CODE 39



FOR FRONT

MADE IN CHINA
DATE CODE: YMM
AFCI PN: 10136956-001LF
CLS REV: 1
CLS PN: R0998-86902-01

FOR BACK

LABEL CONTENTS

ITEM	FCI PART NUMBER	DESCRIPTION	QTY.
7		LABEL	1
6		ACETOUS TAPE, BLACK	1
5	10130517-121LF	MINITEK PWR4.2 HCC RECEPTACLE TERMINAL	24
4	10127815-24LF	MINITEK PWR4.2 REC. HSG, 24 POS., NATURAL	1
3	10132447-121LF	MINITEK PWR3.0 HCC RECEPTACLE TERMINAL	24
2	10132445-24LF	MINITEK PWR3.0 REC. HSG, 24 POS., BLACK	1
1		UL1430 WIRES, MAX. OD 2.2mm, 16 AWG, BLACK	

mat'l. code				surface <input checked="" type="checkbox"/>		tolerance		projection 		product family MINITEK PWR CABLE																			
ltr		ecn no		dr		date		tolerances unless otherwise specified										title											
A				TAI		2016-09-02		angles		linear		X.X±0.5				mm		scale		BBU POWER CABLE, 24 POS. HIGH CURRENT									
												X.XX±0.30																	