


DIMENSIONS



TERMINATION

TIN LEAD PART NUMBER

PART NUMBER

86093967113755122E1


LEAD FREE PART NUMBER

PART NUMBER

86093967113755AHLF

P.C. CARD DRILLING (Component side view)

See drawing ref. C-8609-0000



SPECIFICATION 122 = 6 grounding pins in position :
OR SPECIFICATION AH = row : a-b-c cavity : 1 and 32

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C-8609-0000A

European Views

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	ROUILLARD	2002/09/19	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1.5			
Eng	TARON	2002/09/19			0.XX	±0.1					
Chr	LEGARE	2002/09/19			0.XX' ±2	0.XXX		±0.1			
Appr	LEGARE	2002/09/19	Product family DIN 8609				ECN LS06-0095				
			Spec ref -								
			title STANDARD MALE 3 ROW 96 CONTACTS				dwg no C-8609-1143			Rev C	
			catalog no -				CUSTOMER			sheet 1 of 1	

rev	ecn no	dr	date
A	-	-	2002/09/19
B	LS05-001	JTA	2005/03/04
C	LS06-0095	LGO	2006/06/28
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-