

SCSU2208SLF Faceplates and Panels - FXU SPLITTER



For more Information
please call

1-800-Belden1

General Description:

FX SPLITTER ULTRA CASSETTE, OS2, 2 SPLITTERS, 2 X 08, SC/APC, LC/APC, FRONT

Usage (Overall)

Suitable Applications: FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Related Parts: FX UHD & FXU Patch Panels, FX Patch Cords

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity: 16 Fibers (Output)

Access

Front Connection: 1 inch Pullout

Termination Area: Front

Dimensions**Dimensions:**

Height (mm)	Width (mm)	Length (mm)
38.100	114.300	230.632

Materials**Materials:**

Description	Type	Material	Color
Adapter Sleeve		Zirconia-Ceramic	
Front Connector Body	LC-Duplex w/ Internal Shutters	Plastic - UL94V-0	Green
Front Connector Body	SC-Duplex w/ Shutters	Plastic - UL94V-0	Green
Cassette assy		Plastic - UL94V-0	Black

Weight

Weight: 0.227 kg

Packaging

Packaging: Individually packaged in a plastic shell, Shipped in cardboard box (14/box)

Mechanical Characteristics (Connectivity)

Storage Temperature Range: -10°C To +75°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2013

MII Order #39 (China RoHS): EUP 50

Telecommunications Standards: Telcordia GR-1209-CORE (splitters only), Telcordia GR-1221-CORE (splitters only)

Suitability

Suitability - Indoor: Yes

Transmission Characteristics (Connectivity)**Transmission Specifications:**

Splitter Config.	IL (dB)	Uniformity (dB)	PDL (dB)	Directivity (dB)	RL (dB)
1 x 8	10.7	1.1	0.3	55	55
1 x 16	14.1	1.4	0.3	55	55

SCSU2208SLF Faceplates and Panels - FXU SPLITTER

2 x 8	11.2	1.7	0.4	55	55
2 x 16	14.7	2.1	0.4	55	55
1 x 32	17.0	2.0	0.4	55	55
2 x 32	18.2	2.5	0.5	55	55

Notes (Overall)**Product Family****Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
SCSU2208SLF	1 EA	0.716 LB			FX SPL U CASS OS2 2S 2 X08

Revision Number: 0 Revision Date: 09-06-2016

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.