


Type K PFA Insulated Twin Twisted Pair Thermocouple Cable / Wire (ANSI)

XE-2802-010

10m



TYPE-K

Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

Cable Length	10m
Cable Type	Single pair of PFA insulated conductors twisted together
Core / Strands	1/0.2mm
Conductor Cross Section 1/0.2 (mm²)	0.032
+ Colour	Yellow
- Colour	Red
Drain Wire	No
Insulation Material	PFA Teflon®
Loop Resistance 1/0.2 (Ohms per combined metre)	31.8
Max. Temperature	+260°C
Min. Temperature	-75°C
+ Conductor	Nickel Chromium
- Conductor	Nickel Aluminium
Screen	No
Standards Met	Colour code (cores & jacket) to ANSI MC96.1
Thermocouple Type	K
Tolerance	Class 1

Ordering Information

Type	Style	Material	Core/Strands	Length	Manufacturers Number
K	Twin Twisted	PFA	1/0.2mm	10m (32 ft)	XE-2802-010