

TCNM-AD-1214

TCNM SERIES LASER BARCODE SCANNER



Laser Barcode Scanner AD Std Res High Perf Raster

Range: 50-310 mm; Res.: 6-20 mils

I/O: 2 configurable - NPN/PNP Function Timing

Requires: TCNM-ACBB1 Box or TCNM-AD-CAB Cordset

Part Number: 90813

CERTIFICATIONS



SPECIFICATIONS

IP Rating	IP65
Device Type	Laser
Primary Housing Material	Aluminum
Camera Housing Size (HxWxL mm)	33 x 68 x 83
Code Type	1D
Imager Type	Grayscale
Feature: PC Interface	Yes
RS-232	Yes