

TCNM-AD-2214

TCNM SERIES LASER BARCODE SCANNER



Laser Barcode Scanner AD High Res High Perf
Raster
Range: 45-100 mm; Res.: 5-8 mils
I/O: 2 configurable - NPN/PNP Function Timing
Requires: TCNM-ACBB1 Box or TCNM-AD-CAB
Cordset
Part Number: 90815

CERTIFICATIONS



SPECIFICATIONS

IP Rating	IP65
Device Type	Laser
Primary Housing Material	Aluminum
Camera Housing Size (HxWxL mm)	33 x 68 x 83
Code Type	1D
Imager Type	Grayscale
Feature: PC Interface	Yes
RS-232	Yes