



WT1012

Item No: WT1012N

1-Channel Soldering Station 95 W

KEY FEATURES

- + Power unit, 1 channel with soldering iron WSP 80 and safety rest WSR 201
- + WSP 80 soldering iron (80 W) with Silver-Line tips for all standard soldering applications. Tip family: LT
- + Lock function
- + OFF time, Prozess window, Lock function, Offset

TECHNICAL DATA

Length	5.8 in
Dimensions L x W x H	5.91 x 5.12 x 3.98 In
Automatic Tool Identification	Yes
Equipotential Bonding	Yes
Equipotential Bonding Socket	Via 3.5mm Pawl Socket on Front of Device
ESD Safe	Yes
Fuse	T0.5A
Interface	One Switching Output
Number of Channels	1
Power	95 W
Temperature Accuracy °C	± 9°C
Temperature Accuracy °F	± 17°F
Temperature Range (Depends on Tool)	Adjustable from 50°C - 450°C (150°F - 850°F) Adjustable temperature range varies among tools
Temperature Range °C	50 - 450 °C
Temperature Range °F	150 - 850 °F
Tip Type	LT WT
UPC	037103306562
Voltage	120 V
Weight (Catalog)	1.90 kg
Product Family	WT Line Soldering Stations