

Part#: 0-DURAX

SUPER FINE TWEEZERS - SWITZERLAND - Straight - DURAX

Nickel-Free Alloy - DURAX - Sandblasted - Tips Type: Straight, Pointed, Super Fine - Handle: Classic - ESD-Safe: NO - OAL (mm): 120

DURAX

Technical Information:

Body Material	DURAX
Material Code	1.4034
Category	SUPER FINE TWEEZERS
Hardness	56 +/-2 HRC
Features	Nickel-Free Alloy
Thermal Characteristics	Info on request
ESD-Safe	NO
Coating	Sandblasted
Handle	Classic
Reverse Action	NO
OAL	120.00 mm / 4.72"
Width	10.00 mm / 0.39"
Height	1.50 mm / 0.06"
Weight	13.00 g / 0.46 oz
Tip Material	DURAX
Tip Geometry	Straight
Tip Shape	Pointed
Tip Type	Super Fine
Tip Angle	N/A
Tip Height	0.20 mm / 0.01"
Tip Width	0.30 mm / 0.01"
Tip Serration	NO
Reach/RoHS, and more	YES compliant, on request
HSC	8203.3333
Harmonization Code	8203.20
ECCN	EAR99
UNSPSC Code	27112105
EAN Code	7612947008655
Country of Origin	SWITZERLAND

