

**Part#: 00-SA-FT**

**STRONG TWEEZERS - SWITZERLAND - Straight - STAINLESS STEEL**

Non-Stick, Non-Scratch - STAINLESS STEEL - FULL TEFLON - Tips Type: Straight, Pointed, Thick/Strong - Handle: Classic - ESD-Safe: NO - OAL (mm): 115

TEFLON Coated

## Technical Information:

|                         |                           |
|-------------------------|---------------------------|
| Body Material           | STAINLESS STEEL           |
| Material Code           | 1.4435                    |
| Category                | STRONG TWEEZERS           |
| Hardness                | N/A                       |
| Features                | Non-Stick, Non-Scratch    |
| Thermal Characteristics | Good Temp. Stability      |
| ESD-Safe                | NO                        |
| Coating                 | FULL TEFLON               |
| Handle                  | Classic                   |
| Reverse Action          | NO                        |
| OAL                     | 115.00 mm / 4.53"         |
| Width                   | 10.00 mm / 0.39"          |
| Height                  | 2.50 mm / 0.10"           |
| Weight                  | 22.00 g / 0.78 oz         |
| Tip Material            | STAINLESS STEEL           |
| Tip Geometry            | Straight                  |
| Tip Shape               | Pointed                   |
| Tip Type                | Thick/Strong              |
| Tip Angle               | N/A                       |
| Tip Height              | 0.70 mm / 0.03"           |
| Tip Width               | 0.40 mm / 0.02"           |
| Tip Serration           | NO                        |
| Reach/RoHS, and more    | YES compliant, on request |
| HSC                     | 8203.3333                 |
| Harmonization Code      | 8203.20                   |
| ECCN                    | EAR99                     |
| UNSPSC Code             | 27112105                  |
| EAN Code                | 7612947017190             |
| Country of Origin       | SWITZERLAND               |

