

Part#: 15A-GW

CUTTING TWEEZERS - SWITZERLAND - Angled - CARBON STEEL

Precise and hard - CARBON STEEL - EPOXY - Tips Type: Angled, Slanted Blade, Super Fine - Handle: Classic - ESD-Safe: YES - OAL (mm): 115

Cutting Tweezers

Technical Information:

Body Material	CARBON STEEL
Material Code	C90S
Category	CUTTING TWEEZERS
Hardness	62 +/-2 HRC
Features	Precise and hard
Thermal Characteristics	Info on request
ESD-Safe	YES
Coating	EPOXY
Handle	Classic
Reverse Action	NO
OAL	115.00 mm / 4.53"
Width	11.00 mm / 0.43"
Height	2.50 mm / 0.10"
Weight	30.00 g / 1.06 oz
Tip Material	CARBON STEEL
Tip Geometry	Angled
Tip Shape	Slanted Blade
Tip Type	Super Fine
Tip Angle	50°
Tip Height	0.00 mm / 0.00"
Tip Width	0.00 mm / 0.00"
Tip Serration	NO
Reach/RoHS, and more	YES compliant, on request
HSC	8203.3333
Harmonization Code	8203.20
ECCN	EAR99
UNSPSC Code	27112105
EAN Code	7612947017718
Country of Origin	SWITZERLAND

