

Part#: 3-AXAL-BIO-MED

SUPER FINE TWEEZERS - SWITZERLAND - Straight - AXAL

Antimagnetic/Anti-acid - AXAL - Sandblasted - Tips Type: Straight, Pointed, Super Fine/Biology - Handle: Serrated - ESD-Safe: NO - OAL (mm): 120

Bio-Med Line

Technical Information:

Body Material	AXAL
Material Code	E300
Category	SUPER FINE TWEEZERS
Hardness	N/A
Features	Antimagnetic/Anti-acid
Thermal Characteristics	High Temp. Stability
ESD-Safe	NO
Coating	Sandblasted
Handle	Serrated
Reverse Action	NO
OAL	120.00 mm / 4.72"
Width	10.00 mm / 0.39"
Height	1.50 mm / 0.06"
Weight	13.00 g / 0.46 oz
Tip Material	AXAL
Tip Geometry	Straight
Tip Shape	Pointed
Tip Type	Super Fine/Biology
Tip Angle	N/A
Tip Height	0.05 mm / 0.00"
Tip Width	0.03 mm / 0.00"
Tip Serration	NO
Reach/RoHS, and more	YES compliant, on request
HSC	8203.3333
Harmonization Code	8203.20
ECCN	EAR99
UNSPSC Code	27112105
EAN Code	7612947015677
Country of Origin	SWITZERLAND

