

Part#: 3-SA-FT

SUPER FINE TWEEZERS - SWITZERLAND - Straight - STAINLESS STEEL

Non-Stick, Non-Scratch - STAINLESS STEEL - FULL TEFLON - Tips Type: Straight, Pointed, Super Fine - Handle: Classic - ESD-Safe: NO - OAL (mm): 120

TEFLON Coated

Technical Information:

Body Material	STAINLESS STEEL
Material Code	1.4435
Category	SUPER FINE TWEEZERS
Hardness	N/A
Features	Non-Stick, Non-Scratch
Thermal Characteristics	Good Temp. Stability
ESD-Safe	NO
Coating	FULL TEFLON
Handle	Classic
Reverse Action	NO
OAL	120.00 mm / 4.72"
Width	10.00 mm / 0.39"
Height	1.50 mm / 0.06"
Weight	13.00 g / 0.46 oz
Tip Material	STAINLESS STEEL
Tip Geometry	Straight
Tip Shape	Pointed
Tip Type	Super Fine
Tip Angle	N/A
Tip Height	0.20 mm / 0.01"
Tip Width	0.30 mm / 0.01"
Tip Serration	NO
Reach/RoHS, and more	YES compliant, on request
HSC	8203.3333
Harmonization Code	8203.20
ECCN	EAR99
UNSPSC Code	27112105
EAN Code	7612947013925
Country of Origin	SWITZERLAND

