

BC-M12F5-M12M5-22-1-STP

► DOUBLE-ENDED CORDSETS



Cordset: Double-Ended M12
5-pin Straight Female; 5-pin Straight Male
Connectors
1 m (3.28 ft) 5x22 Black PVC Jacket
Nickel-Plated Brass Coupling Nuts Shielded
Part Number: 816346

SPECIFICATIONS

Cordset Length Range (m)	Less than 2.00
Connector 1 Type	M12
Connector 2 Type	M12
Number of Ends	Double Ended
Connector 1 Number of Contacts	5
Coupling Nut Material	Nickel Plated Brass
Connector 2 Number of Contacts	5
Cable Jacket Material	PVC
Cable Jacket Color	Black
Connector 1 Key Code	A
Connector 2 Key Code	A
Connector 1 Gender	Female
Connector 2 Gender	Male
Cordset Length (m)	1
Connector 1 Orientation	Straight
Connector 2 Orientation	Straight
Overmold Material and Color	PUR Black
Shield/No Shield	Shield - Tied to Pin
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	70
Current Rating (A)	4.0
Supply Voltage	60 V ac/dc