

# BC-M12F5-M12M5-22-2-STP

► DOUBLE-ENDED CORDSETS



Cordset: Double-Ended M12  
5-pin Straight Female; 5-pin Straight Male  
Connectors  
2 m (6.56 ft) 5x22 Black PVC Jacket  
Nickel-Plated Brass Coupling Nuts Shielded  
Part Number: 816576

SPECIFICATIONS

|                                |                      |
|--------------------------------|----------------------|
| Cordset Length Range (m)       | 2.00-4.99            |
| Connector 1 Type               | M12                  |
| Connector 2 Type               | M12                  |
| Number of Ends                 | Double Ended         |
| Connector 1 Number of Contacts | 5                    |
| Coupling Nut Material          | Nickel Plated Brass  |
| Connector 2 Number of Contacts | 5                    |
| Cable Jacket Material          | PVC                  |
| Cable Jacket Color             | Black                |
| Connector 1 Key Code           | A                    |
| Connector 2 Key Code           | A                    |
| Connector 1 Gender             | Female               |
| Connector 2 Gender             | Male                 |
| Cordset Length (m)             | 2                    |
| Connector 1 Orientation        | Straight             |
| Connector 2 Orientation        | Straight             |
| Overmold Material and Color    | PUR Black            |
| Shield/No Shield               | Shield - Tied to Pin |
| Minimum Temp. (Celsius)        | -40                  |
| Maximum Temp. (Celsius)        | 70                   |
| Current Rating (A)             | 4.0                  |
| Supply Voltage                 | 60 V ac/dc           |