

BC-M12F5-M12M5A-22-0.3

DOUBLE-ENDED CORDSETS



Cordset: Double-Ended M12  
5-pin Straight Female A-Code; 5-pin Right-Angle Male A-Code Connectors  
0.3 m (0.98 ft) Black PVC Jacket  
Nickel-Plated Brass Coupling Nuts  
Part Number: 816076

CERTIFICATIONS



SPECIFICATIONS

Cordset Length Range (m)	Less than 2.00
Connector 1 Type	M12
Connector 2 Type	M12
Number of Ends	Double Ended
Connector 1 Number of Contacts	5
Coupling Nut Material	Nickel Plated Brass
Connector 2 Number of Contacts	5
Cable Jacket Material	PVC
Cable Jacket Color	Black
Connector 1 Key Code	A
Connector 2 Key Code	A
Connector 1 Gender	Female
Outside Cable Diameter (mm)	5.6
Connector 2 Gender	Male
Cordset Length (m)	0.3
Connector 1 Orientation	Straight
Connector 2 Orientation	Right Angle
Overmold Material and Color	PUR Black
Shield/No Shield	No Shield