



Product information N11R AM 2 D M20

Industrial Connecting Solutions: Circular Connectors: MIL, DIN, Universal Connectors: DIN 43651 Connectors (NR series): Panel-mounted connector: N11R AM 2 D M20

<https://catalog.beldensolutions.com:443/link/57078-24228-256281-256284-24367-24372-36308/en/conf/uistate>

Name	N11R AM 2 D M20
	Panel-mounted connector with metal screw-in casing (monoblock design), Stifte flüssigkeitsdicht montiert
Delivery informations	
Availability	available
Product description	
Description	Panel-mounted connector with metal screw-in casing (monoblock design), Stifte flüssigkeitsdicht montiert
Type	N11R AM 2 D M20
Order No.	934 338-106
Type of contact	male
Number of contacts	11 + PE
Conductor size	max. 0.5 mm ²
Standard	DIN 43651
Housing Color	grey
Technical data	
Pin dimensions	1.6 mm
Rated voltage	AC/DC 60 V
Rated current	5 A
Contact resistance	<= 5 mOhm
Type of termination	solder, concave pins
Suitable cables	0.14 mm ² to 0.5 mm ²
Mounting	M20x1.5
Material	
Contact surface material	Ag
Contact bearer material	PET
Housing material	PET
Environmental conditions	
Protection class (IEC 60529)	IP 65
Temperature range	-40 °C to +90 °C
Packing unit	
Packaging unit	10 pieces
Scope of delivery and accessories	
Scope of delivery	1 panel-mounted connector with O-Ring in polythene bag with assembly instructions
Accessories to order separately	can be plugged into N11R FF, N11R EF; protective cover SHK 2, order no. 733 845-001



HIRSCHMANN


A BELDEN BRAND

Industrial Connecting Solutions: Circular Connectors: MIL, DIN, Universal Connectors: DIN 43651 Connectors (NR series): Panel-mounted connector: N11R AM 2 D M20

<https://catalog.beldensolutions.com:443/link/57078-24228-256281-256284-24367-24372-36308/en/conf/ui/state>

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.