


P1: M-010



P2: M-005

Customer No: No:1


P1




CONNECTOR: MSL-107




PACKING A:<3M



PACKING B:>3M



PLUG: MSL-202(DIN 49441 YR2 ; CEE 7 Schuko)



MARKING:

H05W-F 3G 0.75mm² ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫ ⑬ ⑭ ⑮ ⑯ ⑰ ⑱ ⑲ ⑳ ㉑ ㉒ ㉓ ㉔ ㉕ ㉖ ㉗ ㉘ ㉙ ㉚ ㉛ ㉜ ㉝ ㉞ ㉟ ㊱ ㊲ ㊳ ㊴ ㊵ ㊶ ㊷ ㊸ ㊹ ㊺ ㊻ ㊼ ㊽ ㊾ ㊿ KEMA-KEUR IEMMEQU <VDE> ㉟

N20050 CTSA-3 3G 0.75mm² MSL

P1: CECC KEMA KEUR DIN FI S OVE

P2: EN 10

NOTE: All relevant materials are complied with RoHS directive .
THE MARKING IS PROTRUDING LETTERING MOULD

3	H05 W-F 3G 0.75mm ² , CTSA-3, 0068mm, JACKET BLACK, DRAWING No. EPH5V0107503C-042	H5TH04-0304K09	1810mm	M304
2	MOLDED PVC 45P, COLOR BLACK	H1BF01-0304K09		M304
	BRACKET: YS-003	A1QC14-0767	1	M767
	TERMINAL: 2x4mm, 98740BS-D/A	A1QB55-0257	3	M257
1	MOLDED PVC 45P, COLOR BLACK	H1BF01-0304K09		M304
	BRACKET: 98651A	A1QA09-0257	1	M257
No.	DESCRIPTION	Q'TY		Supplier

APPROVED				Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201 ~1000mm ±20mm 1001 ~1500mm ±25mm 1501 ~2100mm ±30mm 2100mm↑ ±40mm	
CHECKED	HU				
DESIGNER	XJW				
DRAWING	WEI				
DATE	24/JUL/23	ITEM NO.	AC-112XX		UNIT:mm

△ REV.3 2023.07.24 UPDATE SURFACE

△ REV.1 2017.06.02 MODIFY MSL-107 MOLDED SIZE △ REV.2 2017.07.20 MODIFY CABLE

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm

CHECKED