




P1: M-003

P2: M-005


Customer No: No:1



PLUG: NEMA 5-15P(MSL-105)

IEC 320 C13(MSL-107)

PACKING:



P/N	L(mm)
AC-14-01203-SH	915mm
AC-14-01206-SH	1830mm

MARKING:(UL) SJT 3/C 14AWG(2.08MM²) SHIELDED VW-1 105°C 300V E204978C(UL) SJT 3/C 2.08MM²(14AWG) SHIELDED FT2 105°C 300V E204978 MSL-VN-

105107B2S14B(FP548-01)

P1

P2

L ——— L BLACK
N ——— N WHITE
E ——— E GREEN+DRAIN

P1,P2: cUL E210037-VN

NOTE: All relevant materials are complied with RoHS directive .
THE MARKING IS CONCAVE LETTERING MOULD

3	UL SJT 14AWG*3C + S, OD 9.3mm, JACKET BLACK, DRAWING No. EPSJ141403C-200	H5TC59-0304K09	L-20mm	M304
2	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		
	BRACKET: YS-003	A1QC14-0767	1	M767
	TERMINAL: 2*4mm 98744L	A1QB42-0257	3	M257
1	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		
	BRACKET: YS-002	A1QC07-0767W09	1	M767
	TERMINAL: 98661BS-1	A1QB01-0257	2	M257
	TERMINAL: ø4.75mm, 98475BS-1	A1QB06-0257	1	M257

No.	DESCRIPTION		Q'TY	Supplier
APPROVED				
CHECKED	HU			
DESIGNER	XJW			
DRAWING	WEI			
DATE	08/APR/24	ITEM NO.	AC-14-012XX-SH	

CompuCableUSA

Cable Length
Unless Other Spec.
Tolerances:
0 ~200mm ±10mm
201~1000mm ±20mm
1001 ~1500mm ±25mm
1501~2100mm ±30mm
2100mm± ±40mm

CHECKED

UNIT:mm

