


P1: M-014

P2: M-005


Customer No.:

No.V1



P1



PLUG: MSL-301




CONNECTOR: MSL-107



P2

P1: N21404



MARKING:

H05VV-F 3G 0.75mm² ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ KEMA-KEUR ⑨ IEMMEQU <VDE> ⑩
 N20050 GTSA-3 3G 0.75mm² MSL

P1

P2

L ——— L BROWN
 N ——— N BLUE
 E ——— E GREEN/YELLOW



NOTE: All relevant materials are complied with RoHS directive .
 THE MARKING IS CONCAVE LETTERING MOULD

3	H05VV-F 3G 0.75mm ² GTSA-3, OD 6.8mm, JACKET BLACK, DRAWING No.EPH5V0107503C-042	H5TH04-0304K09	1810mm	M304
2	MOLDED PVC 45P, COLOR BLACK	H1BC02-0304K09		M304
	BRACKET: YS-003	A1QC14-0767	1	M767
	TERMINAL: 2*4mm 98740BS-0/A	A1QB55-0257	3	M257
1	MOLDED PVC 45P, COLOR BLACK	H1BC02-0304K09		M304
	BRACKET: YS-005	A1QC21-0767W09	1	M767
	INSULATOR TERMINAL: P97658BS-1	A1QB13-0257	2	M257
	TERMINAL: 98658BS-1	A1QB21-0257	1	M257
No.	DESCRIPTION	Q'TY		Supplier

APPROVED

CHECKED

HU

DESIGNER

XJW

DRAWING

DAI

DATE

22/DEC/22

ITEM NO.

AC-142XX-AU

Cable Length Unless Other Spec.

Tolerances:

0 ~200mm ±10mm
 201~1000mm ±20mm
 1001 ~1500mm ±25mm
 1501~2100mm ±30mm
 2100mm ±40mm

UNIT:mm



③ REV.3 2017.09.14 MODIFY CABLE & MOLDED LOGO & ENTH ④ REV.4 2022.12.22 MODIFY P2 LOGO

① REV.1 2010.07.20 MODIFY PLUG: MSL-301 PIN APPEAR SIZE ② REV.2 2011.04.12 MODIFY P1&P2 MODEL WORD

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm