

JACKET & MOLDED & BRACKET COLOR	P/N.	LENGTH(Lmm)
BLUE(PT286C) GREEN(PT376C) RED(PT201C) YELLOW(PT123C)	AC-1514-02-XX	610mm
	AC-1514-03-XX	915mm
	AC-1514-04-XX	1220mm
	AC-1514-05-XX	1524mm
	AC-1514-06-XX	1830mm
	AC-1514-07-BU	2134mm
	AC-1514-08-XX	2440mm
	AC-1514-10-XX	3048mm
	AC-1514-15-BU	4570mm

JACKET & MOLDED & BRACKET COLOR	P/N.	LENGTH(Lmm)
BLACK	AC- C1514-XX-XX	XXXmm

PAGE: 2 OF 2

REV.10 2025.06.16	ADD GUEST NUMBER	REV.11 2025.06.25	ADD ITEM
REV.9 2023.10.11	ADD COLOR	REV.10 2025.6.16	MODIFY ITEM LIST
REV.7 2023.07.19	MODIFY CABLE LETTERING CONTENT	REV.8 2023.10.07	MODIFY PRINTING
REV.5 2021.12.13	MODIFY CABLE LETTERING CONTENT	REV.6 2023.06.30	MODIFY MODEL LOGO
REV.3 2015.11.03	MODIFY P2 MODEL LOGO	REV.4 2017.09.04	MODIFY MODEL LOGO & CABLE
REV.1 2013.06.17	MODIFY P2 MODEL LOGO	REV.2 2015.02.04	MODIFY MODEL LOGO

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm

APPROVED		CompuCableUSA	Cable Length Unless Other Spec.	
CHECKED	HU		Tolerances:	
DESIGNER	LM		0 ~200mm	±10mm
DRAWING	PLS		201~1000mm	±20mm
			1001 ~1500mm	±25mm
		1501~2100mm	±30mm	
		2100mm↑	±40mm	
DATE	25/JUN/25	ITEM NO.	AC-C1514-XX-XX & AC-1514-XX-XX	
			UNIT:mm	 