



MARKING: ① ②

(UL) SJT 3/C 14AWG(2.08MM²) VW-1 105°C 300V E204978
 C(UL) SJT 3/C 2.08MM²(14AWG) FT2 105°C 300V E204978 MSL-VN-
 P1,P2: E210037-VN

*NOTE: All relevant materials are complied with RoHS directive .
 THE MARKING IS PROTRUDING LETTERING MOULD

120121B2F14A(FP239-00)			
P1		P2	
L	_____	L	BLACK
N	_____	N	WHITE
E	_____	E	GREEN

P/N	Length(L)	Length(X)
AC-C1520-01	305mm	265mm
AC-C1520-03	915mm	875mm
AC-C1520-06	1830mm	1790mm
AC-C1520-08	2440mm	2400mm
AC-C1520-10	3050mm	3010mm

No.	DESCRIPTION	Q'TY	Supplier
3	UL SJT 14AWG x 3C, OD 9.3mm, JACKET BLACK, DRAWING No. EPSVT011403C-147	Xmm	M304
2	MOLDED PVC 35P, COLOR BLACK		M304
	BRACKET:9745C	1	M257
	TERMINAL:98745L	3	M257
1	MOLDED PVC 35P, COLOR BLACK		M304
	BRACKET: YST-038, COLOR BLACK	1	M767
	TERMINAL: 97607BS-1	1	M257
	TERMINAL: 97606BS-1	2	M257

APPROVED			Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm ↑ ±40mm		
CHECKED	HU				
DESIGNER	XJW				
DRAWING	WEI				
DATE	11/SEP/24	ITEM NO.	AC-C1520-XX	UNIT:mm	

③	REV.3 2024.09.11	MODIFY MOLDED SIZE
②	REV.2 2023.06.06	MODIFY CABLE MARKING MODIFY PLUG LOGO AND LENGTH TOLERANCE & P1 PLUG SIZE
①	REV.1 2022.01.25	MODIFY MARKING
NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm		