

APPROVED		CompuCableUSA		Cable Length Unless Other Spec.		
CHECKED	HU			Tolerances:		
DESINGER	XJW			0 ~200mm	±10mm	
DRAWING	PLS			201~1000mm	±20mm	
				1001 ~1500mm	±25mm	
				1501~2100mm	±30mm	
				2100mm↑	±40mm	
DATE	03/DEC/24	ITEM NO.	AC-L52019-XX		UNIT:mm	 