



P1: M-A08A

P2: M-Q52A


Customer No: No:1

PACKING A: $\leq 1\text{FT}$ PACKING B: OTHER LENGTH
(其他長度)

NEMA 1-15P(MSL-172)



IEC 320 C7(MSL-103)



P/N:

AC-LP13201
AC-LP13203
AC-LP13206
AC-LP13210
AC-LP13215

CABLE MARKING:

(UL) SPT-2 2/C 18AWG(0.824MM²) VW-1 105°C 300V E204978 C(UL)SPT-2 2/C 0.824MM²(18AWG) FT2 105°C 300V E204978 MSL-VN-

103172A2F18A(FP493-00)

P1	P2
L	L
N	N

CHECKED

NOTE: All relevant materials are complied with RoHS directive.

3	UL SPT-2 18AWG x 2C, OD 3.5*6.9mm, JACKET BLACK, DRAWING No. EPSPT001802C-050	H5TA04-0304K09	L-30mm	M304
2	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
	2.35 BRACKET: YS-031, COLOR BLACK	A1QC03-0767K09	1	M767
	2.35 TERMINAL: 98714PS-0	A1QB05-0257	2	M257
1	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
	BRACKET: YST-172-NJ	A1QC95-0767W09	1	M767
	TERMINAL: 98673BBS-1(E)	A1RT08-0257	2	M257

No.	DESCRIPTION		Q'TY	Supplier
APPROVED			Mold Tolerances: 0-5.0±0.3 <5.0±0.5 Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm	
CHECKED	HU			
DESIGNER	ZHU			
DRAWING	PLS			
DATE	29/OCT/24	ITEM NO.	AC-LP132XX	
		UNIT:mm		