


P1: M-084A



Customer No.: No.1



NEMA 5-15P (MSL-158)

PACKING :

MARKING:

(UL) SJT 3/C 18AWG(0.824MM²) VW-1 105°C 300V E204978 C(UL)
 SJT 3/C 0.824MM²(18AWG) FT2 105°C 300V E204978 MSL-VN-

P1: E210037-VN

* NOTE: All relevant materials are complied with RoHS directive .
 THE CABLE MARKING IS CONCAVE LETTERING MOULD

158BB2F18A(FP466-00)	
P1	STRIPPED JACKET 51mm
L	SEMI-STRIPPED 12.7mm BLACK
N	SEMI-STRIPPED 12.7mm WHITE
E	SEMI-STRIPPED 12.7mm GREEN

2	UL SJT 18AWG x 3C, OD 7.8mm, JACKET COLOR SEE LIST, DRAWING No. EPSVT011803C-142	H5TC20-0304K09	1830mm	M304
1	MOLDED PVC 35P, JACKET BLACK	H1BC02-0304K09		M304
	TERMINAL WITH BRACKET: LP-31M内架-9	A1QC82-1035K09	1	M1035

No.	DESCRIPTION	Q'TY	Supplier
APPROVED			
CHECKED	HU		
DESIGNER	XJW		
DRAWING	MuMu		



Cable Length Unless Other Spec.	
Tolerances:	
0 ~200mm	±10mm
201~1000mm	±20mm
1001 ~1500mm	±25mm
1501~2100mm	±30mm
2100mm↑	±40mm

REV.1 2024.07.12 MODIFY PLUG MODEL AND BRACKET SUPPLIER

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm

DATE	12/JUL/24	ITEM NO.	AC-PT18515-XX	UNIT:mm		
------	-----------	----------	---------------	---------	--	--