

EEM-RS485-PCM - Programming adapter



1551889

<https://www.phoenixcontact.com/pc/products/1551889>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

RS-485 USB communication adapter for reading and configuring DC energy meters



Commercial data

Item number	1551889
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CMMC31
GTIN	4067923029361
Weight per piece (including packing)	42 g
Weight per piece (excluding packing)	38 g
Customs tariff number	85176200
Country of origin	DE

EEM-RS485-PCM - Programming adapter



1551889

<https://www.phoenixcontact.com/pc/products/1551889>

Technical data

Product properties

Product type	Programming adapter
--------------	---------------------

Electrical properties

Nominal voltage U_N	5 V (USB)
	12 V (RJ12)
Nominal current I_N	150 mA

Connection data

RS-485	
Connection method	RJ12

Dimensions

Width	25.5 mm
Height	8.4 mm

Cable/line

Cable length	1080 mm
--------------	---------

EEM-RS485-PCM - Programming adapter



1551889

<https://www.phoenixcontact.com/pc/products/1551889>

Classifications

ECLASS

ECLASS-13.0	27371392
-------------	----------

ETIM

ETIM 9.0	EC002498
----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------