





1

2


3

4

5



Specifications:
Current Rating:1.5A AC/DC
Voltage Rating:30V AC/DC
Contact Resistance:30m ohm. Max.
Insulation Resistance:1,000M ohm. min.
Withstanding Voltage:750V AC For One Minute
Operating Temperature Range:-40°C ~ +105°C
Material and Finish
Insulator:PBT(UL94V-0)
Insulator Color:Black
Contact:Brass
Plating:Gold Flash Plated on Contact Area,
Tin Plated on Solder Tail.
Shell:Brass,Nickel Plated
Stainless Steel



RoHS Compliant

F				DRAWN:	GENERAL TOLERANCE:	CnC Tech Industrial Cable and Connector Technology	
E				Jamie Wang	.X=±0.25 .XX=±0.20		
D				CHECKED:	UNIT: MM	DESCRIPTION:	SIZE
C				Jerry Chen	SCALE:1:1	USB A Type PCB Socket Right Angle,G/F	A4
B	05-Aug-2024		Yizhen Lee	APPROVAL:	SHEET: 1 / 2	PART NO:	
A	25-Feb-2018		Jamie Wang	Rory Chen	PROJECTION:	1001-007-01020	
REV	DATE	FILE	BY				



1

2


3

4

5



INNER BAG



Note:

1.Dimension: 400(L)X320(W)X25.0(H) (mm)

Tray Size: 360(L)X280(W)X25.0(H) (mm)


Carton Size:416X330X241 (mm)

2.Quantity:

100pcs/Tray

10Tray/ Carton

Q'TY: 1000pcs



RoHS Compliant

F				DRAWN:	GENERAL TOLERANCE:	CnC Tech Industrial Cable and Connector Technology	
E				Jamie Wang	.X=±0.25 .XX=±0.20		
D				CHECKED:	UNIT: MM	DESCRIPTION:	SIZE
C				Jerry Chen	SCALE:1:1	USB A Type PCB Socket Right Angle,G/F	A4
B	05-Aug-2024		Yizhen Lee	APPROVAL:	SHEET: 2 / 2	PART NO:	
A	25-Feb-2018		Jamie Wang	Rory Chen	PROJECTION:	1001-007-01020	
REV	DATE	FILE	BY				