



P1: M-084A


P2: M-042

Customer No.: NO.1


P1




NEMA 5-15P (MSL-158)



IEC 320 C19(MSL-119)



P2




PACKING A: ≤1FT



PACKING B: ≤2FT



PACKING C: >2FT



MARKING:

(UL) SJT 3/C 14AWG(2.08MM²) VW-1 105°C 300V E204978 C(UL)SJT 3/C 2.08MM²(14AWG) FT2 105°C 300V E204978 MSL-VN-

119158B2F14A(FP405-00)

P1

P2

BLACK	L	_____	L
WHITE	N	_____	N
GREEN	E	_____	E

P1: cULus E210037-VN P2: cULus E210037-VN

NOTE: All relevant materials are complied with RoHS directive .

THE CABLE MARKING IS CONCAVE LETTERING MOULD

3	UL SJT 14AWG x 3C, OD 9.3mm, JACKET BLACK, DRAWING No. EPSVT011403C-147	H5TC21-0304K09	L-30mm	M304
2	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
	BRACKET: YST-037	A1QC36-0767	1	M767
	TERMINAL: 98739ABS-0	A1QB33-0257	3	M257
1	MOLDED PVC BLACK, 35P	H1BC02-0304K09		M304
	TERMINAL WITH BRACKET: LP-31M 内標-9	A1QC82-1035K09	1	M1035

No.	DESCRIPTION	Q'TY	Supplier
APPROVED			
CHECKED	HU		
DESIGNER	XJW		
DRAWING	MuMu		
DATE	12/JUL/24	ITEM NO.	AC-51519-XX

UNIT:mm

Cable Length Unless Other Spec.

Tolerances:

0 ~200mm ±10mm

201~1000mm ±20mm

1001 ~1500mm ±25mm

1501~2100mm ±30mm

2100mm↑ ±40mm

REV.3	2024.07.12	MODIFY P1 PLUG MODEL AND BRACKET SUPPLIER
REV.2	2023.07.27	MODIFY PLUG LETTERING CONTENT & MOLDED SIZE
REV.1	2022.07.12	CANCEL P1 INNER MEMBRANE AND MODIFY P2 MODEL