


P1: M-004


P2: M-028A

Customer No: No:1





PACKING A: ≤1FT

PACKING B: OTHER LENGTH(其它长度)



PACKING C: 指定機器打捆(只有6FT(1.8M))

PACKING D: 10FT以上



106164B2F18D(FP450-03)

	P1		P2
BLACK	L	_____	L
WHITE	N	_____	N
GREEN	E	_____	E



MARKING: (UL) SJT 3/C 18AWG(0.824MM²) VW-1 105°C 300V E204978 C(UL)
SJT 3/C 0.824MM²(18AWG) FT2 105°C 300V E204978 MSL-VN-

P1,P2: αUL E210037-VN

NOTE: All relevant materials are complied with RoHS directive .
THE CABLE MARKING IS CONCAVE LETTERING MOULD

3	UL SJT 18AWG x 3C, OD 7.8mm, JACKET BLACK, DRAWING No. EPSVT011803C-142	H5TC20-0304K09	L-40mm	M304
2	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
	TERMINAL WITH BRACKET:M97723A-3PB	A1QC84-0257K09	1	M257
1	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
	BRACKET: YS-014, COLOR BLACK	A1QC10-0767K09	1	M767
	TERMINAL: 2x4mm 98672BS-1	A1QB07-0257	3	M257
No.	DESCRIPTION			Q'TY Supplier

APPROVED

CHECKED

DESIGNER

DRAWING

DATE

HU

XJW

WEI

27/SEP/22

ITEM NO.

CompuCableUSA

AC-C14C5-XX

Cable Length
Unless Other Spec.
Tolerances:

0 ~200mm	±10mm
201~1000mm	±20mm
1001 ~1500mm	±25mm
1501~2100mm	±30mm
2100mm↑	±40mm

UNIT:mm



NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm

CHECKED